

PREP G EXTRA

UV BLACKOUT PREP

6 December 2017

DESCRIPTION

Simson Prep G Extra is a black Prep, which changes into an opaque and hard film when dry. It has been developed as black Prep for use on glass, not having a ceramic coating, in order to provide a UV-protecting coat, before applying Simson SMP adhesives for bonding Windscreens/windows in the Auto Aftermarket, Automobile, Bus, Ship, and Train industry.

Furthermore Simson Prep G Extra is used for the repair of damaged paint layer on metallic supports (painted metal flange, etc.).

USES

Prep for use on glass, not having a ceramic coating, in order to provide a UV-protecting coat

Use with Simson ISR 70-08 AP

PRODUCT CHARACTERISTICS

Appearance	Smooth Black Liquid
Total Solid	Approx. 30%
Density	Approx. 0.99 g/ml
Dry Time (20°C/50% R.H.)	> 5 minutes
Flash Point	-1°C
Coverage	Approx: 10m ² / L
Product code 250ml can Black	30840125

APPLICATION INSTRUCTIONS

- Application (between 5°C and 30 °C)
- Simson Prep G Extra** dries by evaporation of the solvents and cures on the glass by reaction with moisture.
- Ensure the surface of the glass is clean and dry, dust and grease free. Use a clean, lint and colour free cotton cloth, wet with **Bostik N40 Primer** to wipe the surface of the bond area, leaving a very thin film (discard cotton cloth), then rub the surface with a clean, lint and colour free cotton cloth using a buffing action. Drying time of the film is 3-5 minutes.
- Important Note:** Don't use any activator that has a milky appearance.
- Shake **Simson Prep G Extra** bottle thoroughly for at least 30 seconds or more.
- Open bottle: **Important Note** – Don't use any Prep that has gelled or separated.
- Apply Prep, with a clean dry dauber, evenly in one pass, onto the prepared bond area surface to give a continuous Prep film. Leave to dry for 10 minutes.
- The primed area must be covered by **Simson ISR7008AP** within 3 hours. If it is not applied within 3 hours, reapply the **Simson Prep G Extra** as per above, starting with instruction 4.

REPAIR OF DAMAGED PAINT LAYER

- Ensure the surface of damaged paint layer is clean and dry, dust and grease free.
- Shake **Simson Prep G Extra** Bottle thoroughly for at least 30 seconds or more, open bottle and apply **Simson Prep G Extra** onto damaged area with a dauber.
- Ensure that no Prep is applied to the freshly cut adhesive!
- Leave to dry for 10 minutes before applying the adhesive or before installing the windscreen with adhesive.

PRECAUTIONS

Do not open bottle until ready to use. Use contents within 30 days of opening.
Simson Prep G Extra reacts with the humidity in the air.


PREP G EXTRA

STORAGE & SHELF LIFE

Store in a cool, dry place, out of direct sunlight and away from all sources of ignition. Storage areas must be well ventilated and comply with Local, State and Federal regulations. For maximum shelf life, store between 5°C and 20°C.

Shelf life is up to 9 months when stored in original, unopened containers, under the above conditions.

For emergency information contact the Poisons Information Centre, phone 131 126 or the Emergency Response Service, phone 1800 033 111.



This datasheet is for the general help of users. It is provided in good faith. The data is current and accurate to the best of our knowledge. Differing materials, substrates, environments, site conditions, and product storage, handling and application may affect results. Users should carry out tests to decide the product's suitability for purpose. This data sheet and the properties of the product may change without notice. Users, suppliers and retailers should check that the data sheets they have are the latest. To the maximum extent permitted by law, Bostik disclaims all warranties in relation to manufacture and use of the product. Bostik is not liable for representations made by users, suppliers or retailers about the product. Bostik is not liable for any loss or damage resulting from incorrect, careless, or negligent use or storage of the product, including use of out of date product. Any liability arising from use of the product is limited to the replacement or purchase price of the product. Bostik does not exclude rights and remedies that cannot be excluded by legislation, for example under the Australian Consumer Law (ACL). Sale of the product by Bostik is subject to the Bostik Australia Proprietary Limited Conditions and Terms of Sale. For more information on Bostik, products, and conditions of use and sale visit www.bostik.com/au